

# Eaton QBGFEP2050

Catalog Number: QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFEP2050
<b>UPC</b>	<b>Product Length/Depth</b>
786679145203	5.8 in
<b>Product Height</b>	<b>Product Width</b>
4.4 in	3 in
<b>Product Weight</b>	<b>Warranty</b>
0.9 lb	1 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 943	HACR rated

## Physical Attributes

### Circuit breaker type

QBGFEP

### Mounting Method

Bolt-on

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

30 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

Bolt-on mounting

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBGFEP2050](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)