Specifications



Eaton QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

General specifications	
PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2050
UPC	786679145203
PRODUCT LENGTH/DEPTH	5.8 in
PRODUCT HEIGHT	4.4 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



Physical Attributes	
CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
ТҮРЕ	Ground fault circuit breaker

Performance Ratings	
AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	30 mA trip sensitivity

VOLTA	GE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	Bolt-on mounting

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	QBGFEP2050

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of

Follow us on social media to get the latest product and support information.









