

Specifications

Eaton QBGFT1015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1015
UPC	786680130953
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity

WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al
------------------	--------------------------------

VOLTAGE RATING	120/240 V
-----------------------	-----------

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT1015

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

