

Specifications

Eaton QBGFT1020



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1020
UPC	786680130960
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity

WIRE SIZE#14-10 AWG Cu
#12-10 AWG Al

VOLTAGE RATING120/240 V

Miscellaneous

SPECIAL FEATURES5 mA Trip Sensitivity

Resources

SPECIFICATIONS AND DATASHEETS[Eaton Specification Sheet - QBGFT1020](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

**Eaton Corporation plc**Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton QBGFT1020



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1020
UPC	786680130960
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity

WIRE SIZE#14-10 AWG Cu
#12-10 AWG Al

VOLTAGE RATING120/240 V

Miscellaneous

SPECIAL FEATURES5 mA Trip Sensitivity

Resources

SPECIFICATIONS AND DATASHEETS[Eaton Specification Sheet - QBGFT1020](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

**Eaton Corporation plc**Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

