

# Specifications



Photo is representative



## Eaton QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1040
UPC	786680130991
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#8 Cu #8-6 Al

Performance Ratings	
AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBGFT1040</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications



Photo is representative



## Eaton QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1040
UPC	786680130991
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489

Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#8 Cu #8-6 Al

Performance Ratings	
AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBGFT1040</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

