

Eaton QBGFT2015

Catalog Number: QBGFT2015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications



| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton QB GFCI circuit breaker | QBGFT2015 |
| UPC | Product Length/Depth |
| 786676026703 | 4.5 in |
| Product Height | Product Width |
| 2 in | 2.75 in |
| Product Weight | Warranty |
| 0.6 lb | 1 year |
| Certifications | Catalog Notes |
| UL 489 | HACR rated |

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Ground fault circuit breaker

Wire size

#14-10 AWG Cu

#12-10 AWG Al

Performance Ratings

Amperage Rating

15 A

Interrupt rating

10 kAIC

Trip Type

Common trip

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBGFT2015](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)