

Specifications

Eaton QBGFT2030



Photo is representative

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2030
UPC	786676026734
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
----------------------	------

Performance Ratings

AMPERAGE RATING	30 A
-----------------	------

MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#10 Cu, #8 Al

INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2030

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications

Eaton QBGFT2030



Photo is representative

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2030
UPC	786676026734
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
----------------------	------

Performance Ratings

AMPERAGE RATING	30 A
-----------------	------

MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#10 Cu, #8 Al

INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2030

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

