## **Specifications**



Photo is representative

## Eaton QBGFT2030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Twopole, 120/240V, Common trip, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

| General specifications  | S                             |
|-------------------------|-------------------------------|
| PRODUCT NAME            | Eaton QB GFCI circuit breaker |
| CATALOG NUMBER          | QBGFT2030                     |
| UPC                     | 786676026734                  |
| PRODUCT<br>LENGTH/DEPTH | 4.5 in                        |
| PRODUCT HEIGHT          | 2 in                          |
| PRODUCT WIDTH           | 2.75 in                       |
| PRODUCT WEIGHT          | 0.6 lb                        |
| WARRANTY                | 1 year                        |
| CERTIFICATIONS          | UL 489                        |
| CATALOG NOTES           | HACR rated                    |



| Physical Attributes  |      |  |
|----------------------|------|--|
| CIRCUIT BREAKER TYPE | QBGF |  |

| <b>Performance Ratings</b> |      |
|----------------------------|------|
| AMPERAGE RATING            | 30 A |

| MOUNTING METHOD | Bolt-on                      |
|-----------------|------------------------------|
| NUMBER OF POLES | Two-pole                     |
| ТҮРЕ            | Ground fault circuit breaker |
| WIRE SIZE       | #10 Cu. #8 Al                |

| INTERRUPT RATING | 10 kAIC               |
|------------------|-----------------------|
| TRIP TYPE        | Common trip           |
| TRIP RATING      | 5 mA trip sensitivity |
| VOLTAGE RATING   | 120/240 V             |

| Miscellaneous    |                       |
|------------------|-----------------------|
| SPECIAL FEATURES | 5 mA Trip Sensitivity |

| Resources                     |  |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet -<br>QBGFT2030 |

| PROJECT NAME:   |   |
|-----------------|---|
|                 |   |
| PROJECT NUMBER: |   |
| PREPARED BY:    |   |
|                 | _ |
| DATE:           |   |



**Eaton Corporation plc** 

© 2025 Eaton. All Rights

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







