

Specifications



Eaton QBHW1025

Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,30 A,22 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q17,QBHW

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton QB thermal magnetic circuit breaker |
| CATALOG NUMBER | QBHW1025 |
| UPC | 786679392102 |
| PRODUCT LENGTH/DEPTH | 3.6 in |
| PRODUCT HEIGHT | 4.8 in |
| PRODUCT WIDTH | 1.2 in |
| PRODUCT WEIGHT | 0.35 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL Listed CSA Certified |
| CATALOG NOTES | HACR rated |

| Physical Attributes | |
|----------------------|--|
| CIRCUIT BREAKER TYPE | QBHW |
| MOUNTING METHOD | Bolt-on |
| NUMBER OF POLES | Single-pole |
| TYPE | Quicklag industrial thermal-magnetic circuit breaker |

| Performance Ratings | |
|---------------------|---------------------|
| AMPERAGE RATING | 25 A |
| INTERRUPT RATING | 22 kAIC |
| TRIP TYPE | Non-Interchangeable |
| VOLTAGE RATING | 120/240 V |

| Miscellaneous | |
|---------------|----|
| QUANTITY | 17 |

| Resources | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBHW1025 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton QBHW1025

Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,30 A,22 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q17,QBHW

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton QB thermal magnetic circuit breaker |
| CATALOG NUMBER | QBHW1025 |
| UPC | 786679392102 |
| PRODUCT LENGTH/DEPTH | 3.6 in |
| PRODUCT HEIGHT | 4.8 in |
| PRODUCT WIDTH | 1.2 in |
| PRODUCT WEIGHT | 0.35 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL Listed CSA Certified |
| CATALOG NOTES | HACR rated |

| Physical Attributes | |
|----------------------|--|
| CIRCUIT BREAKER TYPE | QBHW |
| MOUNTING METHOD | Bolt-on |
| NUMBER OF POLES | Single-pole |
| TYPE | Quicklag industrial thermal-magnetic circuit breaker |

| Performance Ratings | |
|---------------------|---------------------|
| AMPERAGE RATING | 25 A |
| INTERRUPT RATING | 22 kAIC |
| TRIP TYPE | Non-Interchangeable |
| VOLTAGE RATING | 120/240 V |

| Miscellaneous | |
|---------------|----|
| QUANTITY | 17 |

| Resources | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBHW1025 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

