

# Specifications



## Eaton QBHW1030

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 35 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW

### General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1030
UPC	786679392157
PRODUCT LENGTH/DEPTH	0.3 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	0.1 in
PRODUCT WEIGHT	0.35 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Quicklag industrial thermal-magnetic circuit breaker

## Miscellaneous

<b>QUANTITY</b>	17
-----------------	----

## Performance Ratings

<b>AMPERAGE RATING</b>	30 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>VOLTAGE RATING</b>	120/240 V

## Resources

<b>CATALOGS</b>	<a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBHW1030</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

