

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

37489 45th Street 74804-0000, OK Shawnee Phone: 405-585-0428 Fax: 405-395-0336



Weight Per each

## QBHW2050 QBHW2P50A B

Eaton Corp

Eaton Corp	
Catalog Number	QBHW2050
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-Pole, 50A, 22 Kaic, 120/240V, Bolt-On
Weight per unit	0.7000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On
Features	
dimensions	3.8000 IN X 2.1000 IN X 4.8000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V
Descriptions	
Description	QBHW2P50A B
extra long description	ETN QBHW2050 QBHW2P50A B
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 50A, 22 kAIC, 120/240V, Bolt-on
Product Type	QBHW2P50A B
Manufacturer Information	
Brand	Eaton
GTIN	00786679392805
Manufacturers Part Number	QBHW2050
UPC	786679392805
Taxonomies, Classifications, and (	Categories
Category Description	PANELBOARD BRANCH BREAKERS
Туре	Thermal magnetic circuit breakers
Packaging	
Carton	1
Package	12

0.7

Fax: 405-395-0336

## Uses, Certifications, and Standards

es, cei lilications, and si	lanuarus
Application	Generation - Renewable Energy - Alternative EnergyGeneration -
	Conventional Energy - Conventional EnergyDatacenters - IT
	Space: CI and Hyper ConvergedOtherMarine Vessels and
	Equipment - Marine Vessels and Equipment - Other
standard	UL Listed, CSA Certified