

# Specifications



## Eaton QBHW2060

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 60A, 22 kAIC, 120/240V , Bolt-on

### General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2060
UPC	786679392904
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.3 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

Performance Ratings	
AMPERAGE RATING	60 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
QUANTITY	7

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW2060</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications



## Eaton QBHW2060

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 60A, 22 kAIC, 120/240V , Bolt-on

### General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW2060
UPC	786679392904
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.3 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

Physical Attributes	
CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Quicklag

Performance Ratings	
AMPERAGE RATING	60 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
QUANTITY	7

Resources	
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW2060</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

