

Eaton QBHW2060

Catalog Number: QBHW2060

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 60A, 22 kAIC, 120/240V , Bolt-on

General specifications



Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW2060
	UPC
	786679392904
Product Length/Depth	Product Height
3.9 in	4.8 in
Product Width	Product Weight
2.3 in	0.7 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag

Performance Ratings

Amperage Rating

60 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QBHW2060](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)