

Eaton QBHW3040H

Catalog Number: QBHW3040H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 40A, 22 kAIC, 240V, Bolt-on



General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW3040H
	UPC
	786679393406
Product Length/Depth	Product Height
3.8 in	4.7 in
Product Width	Product Weight
3.2 in	1.1 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

40 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW3040H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBHW3040H

Catalog Number: QBHW3040H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 40A, 22 kAIC, 240V, Bolt-on



General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW3040H
	UPC
	786679393406
Product Length/Depth	Product Height
3.8 in	4.7 in
Product Width	Product Weight
3.2 in	1.1 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

40 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW3040H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia