



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW3090H 3 Pole 90A QBHW BRKR

Eaton Corp

Catalog Number	QBHW3090H
Manufacturer	Eaton Corp
Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-Pole, 90A, 22 Kaic, 240V, Bolt-On
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 3.2000 IN X 4.8000 IN
interrupt rating	22
Poles	3
Voltage Rating	240 V - 240 V

Descriptions

Description	3 POLE 90A QBHW BRKR
extra long description	ETN QBHW3090H 3 Pole 90 Amp QBHW B
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 90A, 22 kAIC, 240V, Bolt-on
Product Type	3 Pole 90 Amp QBHW Breaker

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786679393604
Manufacturers Part Number	QBHW3090H
UPC	786679393604

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1.1499



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

CSA Certified,UL Listed