

Eaton QBHW3090H

Catalog Number: QBHW3090H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 90A, 22 kAIC, 240V, Bolt-on



General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW3090H |
| | UPC |
| | 786679393604 |
| Product Length/Depth | Product Height |
| 3.9 in | 4.8 in |
| Product Width | Product Weight |
| 3.2 in | 1.15 lb |
| Warranty | Certifications |
| 1 year | CSA Certified |
| | UL Listed |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

90 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QBHW3090H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)