

# Specifications



## Eaton QC2020

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable

### General specifications

|                      |   |
|----------------------|---|
| PRODUCT NAME         | Eaton QC thermal magnetic circuit breaker |
| CATALOG NUMBER       | QC2020                                    |
| UPC                  | 786679309377                              |
| PRODUCT LENGTH/DEPTH | 3.8 in                                    |
| PRODUCT HEIGHT       | 4.8 in                                    |
| PRODUCT WIDTH        | 2.2 in                                    |
| PRODUCT WEIGHT       | 0.65 lb                                   |
| WARRANTY             | 1 year                                    |
| CERTIFICATIONS       | UL Listed<br>CSA Certified                |

| Physical Attributes  |                            |
|----------------------|----------------------------|
| CIRCUIT BREAKER TYPE | QC                         |
| CONNECTION           | Cable-in/cable-out         |
| NUMBER OF POLES      | Two-pole                   |
| TYPE                 | Industrial circuit breaker |

| Performance Ratings |           |
|---------------------|-----------|
| AMPERAGE RATING     | 20 A      |
| INTERRUPT RATING    | 10 kAIC   |
| TRIP TYPE           | T268      |
| VOLTAGE RATING      | 120/240 V |

| Miscellaneous |                     |
|---------------|---------------------|
| OPTIONS       | Non-interchangeable |

| Resources                     |  |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - QC2020</a> |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| DATE:           |



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications



## Eaton QC2020

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable

### General specifications

|                      |   |
|----------------------|---|
| PRODUCT NAME         | Eaton QC thermal magnetic circuit breaker |
| CATALOG NUMBER       | QC2020                                    |
| UPC                  | 786679309377                              |
| PRODUCT LENGTH/DEPTH | 3.8 in                                    |
| PRODUCT HEIGHT       | 4.8 in                                    |
| PRODUCT WIDTH        | 2.2 in                                    |
| PRODUCT WEIGHT       | 0.65 lb                                   |
| WARRANTY             | 1 year                                    |
| CERTIFICATIONS       | UL Listed<br>CSA Certified                |

| Physical Attributes  |                            |
|----------------------|----------------------------|
| CIRCUIT BREAKER TYPE | QC                         |
| CONNECTION           | Cable-in/cable-out         |
| NUMBER OF POLES      | Two-pole                   |
| TYPE                 | Industrial circuit breaker |

| Performance Ratings |           |
|---------------------|-----------|
| AMPERAGE RATING     | 20 A      |
| INTERRUPT RATING    | 10 kAIC   |
| TRIP TYPE           | T268      |
| VOLTAGE RATING      | 120/240 V |

| Miscellaneous |                     |
|---------------|---------------------|
| OPTIONS       | Non-interchangeable |

| Resources                     |  |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - QC2020</a> |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| DATE:           |



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

