

# Specifications

## Eaton QC2030

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, QC, Non-interchangeable



### General specifications

<b>PRODUCT NAME</b>	Eaton QC thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QC2030
<b>UPC</b>	786679309469
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3.125 in
<b>PRODUCT WEIGHT</b>	0.75 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide

## Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

## Miscellaneous

OPTIONS	Non-interchangeable
---------	---------------------

## Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QC2030</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QC2030

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, QC, Non-interchangeable



### General specifications

<b>PRODUCT NAME</b>	Eaton QC thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QC2030
<b>UPC</b>	786679309469
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3.125 in
<b>PRODUCT WEIGHT</b>	0.75 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide

## Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

## Miscellaneous

OPTIONS	Non-interchangeable
---------	---------------------

## Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QC2030</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

