

# Eaton QCR2030

Catalog Number: QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton QCR thermal magnetic circuit breaker	QCR2030
	UPC
	786679144343
<b>Product Length/Depth</b>	<b>Product Height</b>
4.6 in	1.2 in
<b>Product Width</b>	<b>Product Weight</b>
3.3 in	0.5 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	HACR Rated
<b>Certifications</b>	<b>Catalog Notes</b>
CSA Certified UL Listed	Standard breaker terminals are box type lugs.

## Physical Attributes

### Circuit breaker type

QCR

### Connection

Cable-in/cable-out

### Mounting Method

Rear

### Number of poles

Two-pole

### Terminals

Fixed

### Type

Industrial circuit breaker

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Trip Type

Thermal-magnetic

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QCR2030](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)