

# Specifications



## Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

### General specifications

PRODUCT NAME	Eaton QCR thermal magnetic circuit breaker
CATALOG NUMBER	QCR2030
UPC	786679144343
PRODUCT LENGTH/DEPTH	4.6 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
COMPLIANCES	HACR Rated
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Standard breaker terminals are box type lugs.



Powering Business Worldwide

Physical Attributes	
CIRCUIT BREAKER TYPE	QCR
CONNECTION	Cable-in/cable-out
MOUNTING METHOD	Rear
NUMBER OF POLES	Two-pole
TERMINALS	Fixed
TYPE	Industrial circuit breaker

Performance Ratings	
AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources	
CATALOGS	<a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QCR2030</a>

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

Follow us on social media to get the latest product and support information.

