



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



R26USBCC6W Rad C/C Fast Charge Usb + Duplex 15A WH

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | R26USBCC6W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 6.0A Ultra-Fast Type C/C Usb Chargers With Duplex 15A Tamper-Resistant Outlet, White |
| Weight per unit | 0.3392 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|----------------|---|
| indoor/outdoor | Indoor |
| media | Yes |
| Mounting Type | Box |
| Outlet Type | Residential, USB-Charging, Tamper-Resistant, Indoor |
| Poles | Double Pole |
| Voltage | 125.0 V |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | Matte |

Descriptions

| | |
|------------------------|---|
| Description | RAD C/C FAST CHARG USB + DUPLEX 15A WH |
| extra long description | P&S R26USBCC6W RAD C/C FAST CHARG U |
| Features | USB-C Charging |
| Long Description | 6.0A Ultra-Fast Type C/C USB Chargers with Duplex 15A Tamper-Resistant Outlet, White |
| Product Type | Rad C/C Fast Charge Usb + Dup 15A W |
| Special Features | Ultra-Fast USB Charging |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007207750 |
| Manufacturers Part Number | R26USBCC6W |
| UPC | 785007207750 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3392 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | 95% (relative humidity, non-condensing) |
| nema rating | 15A |
| standard | UL, cULus |