

Eaton RACH24L125I

Catalog Number: RACH24L125I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

General specifications



Photo is representative

Product Name

Eaton CH retrofit kit

UPC

786685211060

Product Height

30 in

Product Weight

1 lb

Certifications

UL 67

Catalog Number

RACH24L125I

Product Length/Depth

6 in

Product Width

22 in

Warranty

1 year

Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

Product specifications

Type

Retrofit kit

Amperage Rating

125 A

Main circuit breaker

CH

Mounting

Surface, flush

Number of circuits

24

Phase

Single-phase

Wire size

#4-2/0 AWG

Box size

Retro size group a

Cover height

33

Cover width

24

Enclosure

NEMA 1

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - RACH24L125I](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton RACH24L125I

Catalog Number: RACH24L125I

Eaton CH 3/4-inch Loadcenter Retrofit Stacking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

General specifications



Photo is representative

Product Name

Eaton CH retrofit kit

UPC

786685211060

Product Height

30 in

Product Weight

1 lb

Certifications

UL 67

Catalog Number

RACH24L125I

Product Length/Depth

6 in

Product Width

22 in

Warranty

1 year

Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

Product specifications

Type

Retrofit kit

Amperage Rating

125 A

Main circuit breaker

CH

Mounting

Surface, flush

Number of circuits

24

Phase

Single-phase

Wire size

#4-2/0 AWG

Box size

Retro size group a

Cover height

33

Cover width

24

Enclosure

NEMA 1

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - RACH24L125I](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)