

Specifications

Photo is representative

Eaton RACH24L125I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

Product specifications

TYPE	Retrofit kit
AMPERAGE RATING	125 A
MAIN CIRCUIT BREAKER	CH
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	24
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG
BOX SIZE	Retro size group a
COVER HEIGHT	33
COVER WIDTH	24
ENCLOSURE	NEMA 1

General specifications

PRODUCT NAME	Eaton CH retrofit kit
CATALOG NUMBER	RACH24L125I
UPC	786685211060
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	30 in
PRODUCT WIDTH	22 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
CERTIFICATIONS	UL 67
CATALOG NOTES	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



Powering Business Worldwide

Specifications

Photo is representative

Eaton RACH24L125I

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main lug only, 125 A, size group a, Cover height: 33 in, Cover width: 24 in, NEMA 1, CH, Surface, flush, 24 Circuits, Single-phase, 0.75 in, #4-2/0 AWG

Product specifications

TYPE	Retrofit kit
AMPERAGE RATING	125 A
MAIN CIRCUIT BREAKER	CH
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	24
PHASE	Single-phase
WIRE SIZE	#4-2/0 AWG
BOX SIZE	Retro size group a
COVER HEIGHT	33
COVER WIDTH	24
ENCLOSURE	NEMA 1

General specifications

PRODUCT NAME	Eaton CH retrofit kit
CATALOG NUMBER	RACH24L125I
UPC	786685211060
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	30 in
PRODUCT WIDTH	22 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
CERTIFICATIONS	UL 67
CATALOG NOTES	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



Powering Business Worldwide