



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville  
72802-0000, AR Russellville  
Phone: 479-967-2303  
Fax: 479-967-2306



## RC1010FL 12-10 Ins Nylon Spade Term

*Abb Installation Products, Inc*

Catalog Number	RC1010FL
Manufacturer	Abb Installation Products, Inc
Description	Nylon Insulated Locking Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated
Weight per unit	0.0060 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

Material	Copper
Voltage Rating	600 V
Wire Size	12-10 AWG

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	12-10 INS NYLON SPADE TERM
extra long description	ABB RC10-10FL INSNYL LKG FORK TERM
Long Description	Nylon Insulated Locking Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated
Product Type	Insnyl LKG Fork Term 12-10 NO10 Yel
Special Features	Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring

### Manufacturer Information

Brand	Sta-Kon
GTIN	00786210887531
Manufacturers Part Number	RC10-10FL
UPC	786210887531

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Nylon Insulated Locking Fork Terminal

### Availability

minimum qty	50
-------------	----

### Packaging

Carton	50
Package	250
Weight Per each	0.006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville  
72802-0000, AR Russellville  
Phone: 479-967-2303  
Fax: 479-967-2306

---

## Uses, Certifications, and Standards

standard

UL E9809 / UL E9809

---