

GROUNDING

Ground Clamps

Heavy Duty Direct Burial with Adapters & Rebar
G-S-DBR, G-BS, RC Series



SPECIFICATIONS

Heavy Duty Bronze Ground Clamp (G-S DBR)

- cULus Listed 467 Grounding & Bonding.
- UL467 Listed, Grounding & Bonding.

HD Ground Clamp With Adapter & Brass Screws (G-BS)

- cULus Listed 467 Grounding & Bonding.
- UL467 Listed, Grounding & Bonding.

Ground Clamp With Adapter & Brass Screws (RC)

- cULus Listed 467 Grounding & Bonding/Direct Bury.
- UL467 Listed, Grounding & Bonding.
- *UL Listed for #4 STR - #2 STR.
- **Application:** For use with copper wire only. Harsh direct bury environments & Pool and Spa. Any commercial, industrial, maintenance application where ground wire needs to be connected to rebar.

FEATURES

Heavy Duty Bronze Ground Clamp (G-S DBR)


- Bronze ground clamp for bonding bare copper wire to copper water pipe.
- Assembled with tough 304 stainless steel screws.
- Available with silicon bronze screws by adding suffix -SB.

HD Ground Clamp With Adapter & Brass Screws (G-BS)

- Bronze clamps for copper water pipes with bronze adapters.
- Assembled with brass screws.

Ground Clamp With Adapter & Brass Screws (RC)

- Lay-in style clamp allows for continuous loop wiring.
- Cast silicon bronze connector & Stainless steel hardware.



CAT. NO.	FIG. NO.	CERTIFICATION	GROUND WIRE RANGE (IN.)	PIPE SIZE (IPS) (IN.)	REBAR SIZE (IN.)	GROUND ROD SIZE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
G-1-SDBR	1	cULus	10 SOL - 2 STR	1/2-1	3/8 - 1	3/8-1	2.280	0.650	1.400	20
G-2BS	2	UL	8-4/0 STR	1/2-1	-	-	2.320	0.748	1.437	20
G-3BS	2	cULus	8-4/0 STR	1/2-1	-	-	2.320	0.748	1.437	20
RC38	3	cULus	8-6 SOL	-	3/8	-	1.14	0.74	0.75	25
RC50	4	cULus	8 SOL - 4 STR	-	1/2	-	1.35	0.83	0.91	25
RC58*	5	UL	6 SOL - 2/0 STR	-	5/8	-	1.62	0.80	1.06	25



Scan QR code
for mobile access to
Grounding drawings.