



## TWO SINGLE POLE SWITCHES, WHITE

RCD11W | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Unique "Up/Down" switches match the look and feel of radiant paddle switches.
- Easy-to-use oversized main switch for primary load.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- Impact-resistant face and body.
- Full wraparound metal strap, commercial grade with lock-in tabs.
- All screws are tri-drive.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Largest breadth of 15 amp offering.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Combination

Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
cULus: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121704

#### CONSTRUCTION INFORMATION

Component 4: 78500705489

#### DIMENSIONS

Depth (US): 1.43"  
Height (US): 3.81"  
Width (US): 1.29

#### TECHNICAL INFORMATION

Amps: 15A  
Volts: 120VAC



## TWO SINGLE POLE SWITCHES, WHITE

RCD11W | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.



- Part of the all-new radiant® collection.
- Unique "Up/Down" switches match the look and feel of radiant paddle switches.
- Easy-to-use oversized main switch for primary load.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- Impact-resistant face and body.
- Full wraparound metal strap, commercial grade with lock-in tabs.
- All screws are tri-drive.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Largest breadth of 15 amp offering.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Combination

Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
cULus: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121704

#### **CONSTRUCTION INFORMATION**

Component 4: 78500705489

#### **DIMENSIONS**

Depth (US): 1.43"  
Height (US): 3.81"  
Width (US): 1.29

#### **TECHNICAL INFORMATION**

Amps: 15A  
Volts: 120VAC