



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD38TRW Radiant SP/3WAY SW+15A TR Outlet WH *Pass & Seymour/Legrand*

|                  |                                                                                   |
|------------------|-----------------------------------------------------------------------------------|
| Catalog Number   | RCD38TRW                                                                          |
| Manufacturer     | Pass & Seymour/Legrand                                                            |
| Description      | 15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, White |
| Weight per unit  | 0.2083 (lbs/each)                                                                 |
| Product Category | Gen Purpose Switches                                                              |

### Features

|                       |                  |
|-----------------------|------------------|
| actuator              | Rocker switch    |
| amperage rating       | 15               |
| Contact Configuration | 15A              |
| Contact Rating        | 125              |
| indoor/outdoor        | Indoor           |
| media                 | Yes              |
| Mounting Type         | Box              |
| Number of Gangs       | 1.0              |
| Number of Switches    | 1.0              |
| operating cycles      | 50000            |
| Outlet Type           | Tamper-Resistant |
| Poles                 | Single Pole      |
| Switch Type           | Push             |
| Voltage               | 120.0 V          |
| Voltage Rating        | 125              |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | Matte |

### Dimensions and Weight

|      |                                          |
|------|------------------------------------------|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|------------------------------------------|

### Descriptions

|                        |                                                                                   |
|------------------------|-----------------------------------------------------------------------------------|
| Description            | RADIANT SP/3WAY SW+15A TR OUTLET WH                                               |
| extra long description | P&S RCD38TRW RADIANT SP/3WAY SW+15A                                               |
| Features               | Combination, Locator Light                                                        |
| Long Description       | 15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, White |
| Product Type           | Radiant SP/3WAY SW+15A TR Outlet WH                                               |
| Special Features       | Single Pole 3-Way Switch                                                          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007055085         |
| Manufacturers Part Number | RCD38TRW               |
| UPC                       | 785007055085           |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | Switch, Outlet     |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 12     |
| Weight Per each | 0.2083 |

## Uses, Certifications, and Standards

|                          |                                          |
|--------------------------|------------------------------------------|
| Application              | Residential                              |
| environmental conditions | Flammability Rating: UL 94 V2            |
| Mounting                 | BOX                                      |
| nema rating              | 15A                                      |
| Operating Temperature    | Maximum continuous +115°C, minimum -40°C |
| standard                 | CULUS, UL, cULus, UL Listed              |