



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Z-Wave Smart Accessory Dimmer

RF9542-ZDW

UPC:032664739101

### Dimensions:

- **Height:** 4.2 IN
- **Length:** 1.8 IN
- **Width:** 1.36 IN

**Weight:** .28 LB

### Warranties:

- 2 year limited

### Specifications:

- **Special Features:** 7-step LED light level display
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Actuator:** Push pad
- **Closure Type:** Maintained
- **Color:** White
- **Load Type:** Fan, LED, INC, CFL, ELV, MLV, FLR, Halogen
- **Number Of Poles:** Single-pole
- **Number of Ways:** Three-way
- **Phase:** Single-phase
- **Switch Type:** Multi-location
- **Material:** Polycarbonate

**Supporting documents:** No Data

### Certifications:

- cULus Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Z-Wave Smart Accessory Dimmer

RF9542-ZDW

UPC:032664739101

### Dimensions:

- **Height:** 4.2 IN
- **Length:** 1.8 IN
- **Width:** 1.36 IN

**Weight:** .28 LB

### Warranties:

- 2 year limited

### Specifications:

- **Special Features:** 7-step LED light level display
- **Mounting Type:** Flush
- **Voltage Rating:** 120V
- **Wiring Method:** Wire lead
- **Actuator:** Push pad
- **Closure Type:** Maintained
- **Color:** White
- **Load Type:** Fan, LED, INC, CFL, ELV, MLV, FLR, Halogen
- **Number Of Poles:** Single-pole
- **Number of Ways:** Three-way
- **Phase:** Single-phase
- **Switch Type:** Multi-location
- **Material:** Polycarbonate

**Supporting documents:** No Data

### Certifications:

- cULus Listed

**Product compliance:** No Data



