

# Specifications

## Eaton RFS5-W

Eaton fan speed controller, Power failure memory, non-preset, Fully variable, #16 AWG, 5A, 120V, Wire lead, Maintained closure, White, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton fan speed controller
<b>CATALOG NUMBER</b>	RFS5-W
<b>UPC</b>	032664699290
<b>PRODUCT LENGTH/DEPTH</b>	2.3 in
<b>PRODUCT HEIGHT</b>	4.75 in
<b>PRODUCT WIDTH</b>	3.08 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	cULus Listed
<b>PRODUCT TYPE</b>	Fan speed controller



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	5 A
FREQUENCY RATING	60 Hz
LOAD TYPE	INC HAL
VOLTAGE RATING	120 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#16 AWG
MOUNTING METHOD	Flush
WIRING METHOD	Wire lead

## Product Specifications

TYPE	Fully variable
------	----------------

## Environmental Specifications

ENVIRONMENTAL CONDITIONS	Indoor
--------------------------	--------

## Material Specifications

COLOR	White
MATERIAL	Polycarbonate

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RFSS-W</a> <a href="#">Rotary dimmers and fan controls spec sheet</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton RFS5-W

Eaton fan speed controller, Power failure memory, non-preset, Fully variable, #16 AWG, 5A, 120V, Wire lead, Maintained closure, White, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, Polycarbonate

### General specifications

<b>PRODUCT NAME</b>	Eaton fan speed controller
<b>CATALOG NUMBER</b>	RFS5-W
<b>UPC</b>	032664699290
<b>PRODUCT LENGTH/DEPTH</b>	2.3 in
<b>PRODUCT HEIGHT</b>	4.75 in
<b>PRODUCT WIDTH</b>	3.08 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	cULus Listed
<b>PRODUCT TYPE</b>	Fan speed controller



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	5 A
FREQUENCY RATING	60 Hz
LOAD TYPE	INC HAL
VOLTAGE RATING	120 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#16 AWG
MOUNTING METHOD	Flush
WIRING METHOD	Wire lead

## Product Specifications

TYPE	Fully variable
------	----------------

## Environmental Specifications

ENVIRONMENTAL CONDITIONS	Indoor
--------------------------	--------

## Material Specifications

COLOR	White
MATERIAL	Polycarbonate

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RFSS-W</a> <a href="#">Rotary dimmers and fan controls spec sheet</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

