

Specifications

Eaton RFS5-W

Eaton fan speed controller, Power failure memory, non-preset, Fully variable, #16 AWG, 5A, 120V, Wire lead, Maintained closure, White, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, Polycarbonate

General specifications

PRODUCT NAME	Eaton fan speed controller
CATALOG NUMBER	RFS5-W
UPC	032664699290
PRODUCT LENGTH/DEPTH	2.3 in
PRODUCT HEIGHT	4.75 in
PRODUCT WIDTH	3.08 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Fan speed controller



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	5 A
FREQUENCY RATING	60 Hz
LOAD TYPE	INC HAL
VOLTAGE RATING	120 V

Installation Specifications

ALLOWABLE WIRE SIZE	#16 AWG
MOUNTING METHOD	Flush
WIRING METHOD	Wire lead

Product Specifications

TYPE	Fully variable
------	----------------

Environmental Specifications

ENVIRONMENTAL CONDITIONS	Indoor
--------------------------	--------

Material Specifications

COLOR	White
MATERIAL	Polycarbonate

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RFSS-W Rotary dimmers and fan controls spec sheet
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

