

Round Head Machine Screws • Slotted/Phillips Combo Zinc-Plated Steel

CATALOG NUMBER*	UPC NUMBER	DIAMETER	LENGTH	STD PAK [◇] PCS/PKG	PKG STYLE*	CASE QTY	WEIGHT/PKG (lbs.)
* RH614J	78103551011	6-32	1/4	100	Jar	48 Jars	0.23
RH638J	78103551013	6-32	3/8	100	Jar	48 Jars	0.26
RH612J	78103551014	6-32	1/2	100	Jar	48 Jars	0.28
RH634J	78103551016	6-32	3/4	100	Jar	48 Jars	0.36
RH611J	78103551017	6-32	1	100	Jar	48 Jars	0.45
RH6114J	78103551018	6-32	1-1/4	100	Jar	48 Jars	0.50
RH6112J	78103551019	6-32	1-1/2	100	Jar	48 Jars	0.58
RH62J	78103551021	6-32	2	100	Jar	48 Jars	0.73
RH6212J	78103551022	6-32	2-1/2	100	Jar	36 Jars	0.87
RH63J	78103551023	6-32	3	100	Jar	36 Jars	1.01
RH838J	78103551029	8-32	3/8	100	Jar	48 Jars	0.36
RH812J	78103551030	8-32	1/2	100	Jar	48 Jars	0.41
RH834J	78103551031	8-32	3/4	100	Jar	48 Jars	0.50
RH81J	78103551032	8-32	1	100	Jar	48 Jars	0.63
RH8114J	78103551033	8-32	1-1/4	100	Jar	48 Jars	0.72
RH8112J	78103551034	8-32	1-1/2	100	Jar	48 Jars	0.84
* RH8134J	78103551035	8-32	1-3/4	100	Jar	48 Jars	0.96
RH82J	78103551036	8-32	2	100	Jar	48 Jars	1.01
RH8212J	78103551037	8-32	2-1/2	100	Jar	36 Jars	1.27
RH83J	78103551038	8-32	3	100	Jar	36 Jars	1.54
* RH1038J	78103551041	10-24	3/8	100	Jar	48 Jars	0.49
RH1012J	78103551042	10-24	1/2	100	Jar	48 Jars	0.56
RH1034J	78103551044	10-24	3/4	100	Jar	48 Jars	0.70
RH101J	78103551045	10-24	1	100	Jar	48 Jars	0.84
RH10114J	78103551046	10-24	1-1/4	100	Jar	48 Jars	1.04
RH10112J	78103551047	10-24	1-1/2	100	Jar	48 Jars	1.11
RH102J	78103551049	10-24	2	100	Jar	36 Jars	1.34
RH10212J	78103551050	10-24	2-1/2	100	Jar	36 Jars	1.65
RH103J	78103551051	10-24	3	100	Jar	24 Jars	1.96
RH104J	78103551053	10-24	4	100	Jar	12 Jars	2.56
RH138J	78103551057	10-32	3/8	100	Jar	48 Jars	0.48
RH112J	78103551058	10-32	1/2	100	Jar	48 Jars	0.56
RH134J	78103551060	10-32	3/4	100	Jar	48 Jars	0.72
RH11J	78103551061	10-32	1	100	Jar	48 Jars	0.91
RH1114J	78103551062	10-32	1-1/4	100	Jar	48 Jars	1.05
RH1112J	78103551063	10-32	1-1/2	100	Jar	48 Jars	1.15
RH12J	78103551064	10-32	2	100	Jar	36 Jars	1.50
* RH1212J	78103551066	10-32	2-1/2	100	Jar	36 Jars	1.77
* RH13J	78103551900	10-32	3	100	Jar	24 Jars	2.10
* RH14J	78103551904	10-32	4	100	Jar	12 Jars	2.81
RH1438J	78103551067	1/4-20	3/8	100	Jar	48 Jars	0.91
RH1412J	78103551068	1/4-20	1/2	100	Jar	48 Jars	1.02
RH1434J	78103551070	1/4-20	3/4	100	Jar	48 Jars	1.34
RH141J	78103551071	1/4-20	1	100	Jar	48 Jars	1.51
RH14114J	78103551072	1/4-20	1-1/4	100	Jar	48 Jars	1.74
RH14112J	78103551073	1/4-20	1-1/2	100	Jar	36 Jars	2.04
RH14134J	78103551074	1/4-20	1-3/4	100	Jar	36 Jars	2.30
RH142J	78103551075	1/4-20	2	100	Jar	24 Jars	2.58
RH14212J	78103551076	1/4-20	2-1/2	100	Jar	12 Jars	3.05
RH143J	78103551077	1/4-20	3	50	Jar	12 Jars	1.80
RH144J	78103551079	1/4-20	4	50	Jar	24 Jars	2.33
* RH5161J	78103551085	5/16-18	1	100	Jar	36 Jars	2.64
RH3812J	78103551090	3/8-16	1/2	100	Jar	36 Jars	2.75
RH3834J	78103551091	3/8-16	3/4	100	Jar	36 Jars	3.55
RH381J	78103551092	3/8-16	1	100	Jar	24 Jars	4.14
RH38114J	78103551093	3/8-16	1-1/4	100	Jar	12 Jars	4.88
RH38112J	78103551094	3/8-16	1-1/2	100	Jar	12 Jars	5.09
RH382J	78103551096	3/8-16	2	100	Jar	12 Jars	6.42
RH38212J	78103551098	3/8-16	2-1/2	100	Jar	12 Jars	7.62
RH383J	78103551200	3/8-16	3	50	Jar	12 Jars	4.46
RH384J	78103551204	3/8-16	4	50	Jar	12 Jars	5.73



* Sizes slotted only

+ Jar version part number shown. Box and Bulk versions may be available. Contact Selecta for availability, part number and pricing.

◇ Other quantities per individual package may be available. Contact Selecta for details.