



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RN125 1-1/4" Offset Nipple

*Appleton/Oz Gedney*

|                  |   |
|------------------|---|
| Catalog Number   | RN125   |
| Manufacturer     | Appleton/Oz Gedney  |
| Description      | Features:1.84IN Dia X 2.9IN Length, For Cabinets, Enclosures,<br>Standard:UI 514B, Csa C22.2, Nema FB-1, Size:1.25IN,<br>Material:Die Cast Zinc |
| Weight per unit  | 0.3000 (lbs/each)   |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|          |               |
|----------|---------------|
| Material | Die Cast Zinc |
|----------|---------------|

### Dimensions and Weight

|      |      |
|------|------|
| Size | 1.25 |
|------|------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1-1/4" OFFSET NIPPLE  |
| extra long description | EGS RN-125 1-1/4 IN 3/4 O/S NIP ZNC   |
| Long Description       | Features:1.84IN Dia X 2.9IN Length, For Cabinets, Enclosures,<br>Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.25IN,<br>Material:Die Cast Zinc |
| Product Type           | 1-1/4 In 3/4 O/S Nip ZNC D/C  |
| Special Features       | 1.84 IN Dia X 2.9 IN Length, For Cabinets, Enclosures   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Appleton       |
| GTIN                      | 00687855291250 |
| Manufacturers Part Number | RN125          |
| UPC                       | 687855291250   |

### Taxonomies, Classifications, and Categories

|                      |                                |
|----------------------|--------------------------------|
| Category Description | DIECAST OFFSET & CHASE NIPPLES |
| Type                 | Offset Nipple                  |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 5   |
| Package         | 50  |
| Weight Per each | 0.3 |

### Uses, Certifications, and Standards

|          |                               |
|----------|-------------------------------|
| standard | UL 514B, CSA C22.2, NEMA FB-1 |
|----------|-------------------------------|