

Eaton S10N06A83N

Catalog Number: S10N06A83N

Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 55, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.15 KVA, indoor-outdoor, 3C

General specifications



Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S10N06A83N
	UPC
	786680383182

Product Length/Depth	Product Height
4 in	8.91 in

Product Width	Product Weight
4.11 in	8 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Catalog Notes
	Model N

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

55

Tap size

None

Type

Buck-Boost General-Purpose Encapsulated Transformer

Wiring connection

3C

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

16/32 V

Temperature rise

115 °C rise

Volt ampere rating

0.15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Specifications and datasheets

[Eaton Specification Sheet - S10N06A83N](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)