



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11258 Wi-Fi 15W Led Par 38 RGB/Tunable Flood

Satco

Catalog Number	S11258
Manufacturer	Satco
Description	15 Watt - PAR38 Led Lamp - RGB and Tunable White - Starfish lot - 120 Volts - 1200 Lumens
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	E26
beam angle	40
dimnable	Yes-Dimmable
lumens	1200
Material	Plastic
Power Factor	0.9
Shape	PAR38
Voltage Rating	120
Warranty	3 Year Limited - 3 hr per day
Wattage	15

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	2700 to 5000
Finish	white

Dimensions and Weight

Size	5
------	---

Descriptions

Description	WI-FI 15W LED PAR 38 RGB/TUNABLE FLOOD
extra long description	SATCO S11258 15PAR38/LED/RGB/TW/SF
Long Description	15 Watt - PAR38 LED Lamp - RGB and Tunable White - Starfish IOT - 120 Volts - 1200 Lumens
Product Type	15PAR38/Led/RGB/TW/SF
Special Features	Warranty: 5-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: Only with Starfish App ; Material: Plastic ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Warm to Cool White/Color Changeable ; Efficacy: 80.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: E26 ; Amps: 0.125A ; T24 Compliant: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923112584
Manufacturers Part Number	S11258
UPC	045923112584

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
Type	LED Directional

Packaging

Carton	1
Weight	0.33
Weight Per each	1.21

Uses, Certifications, and Standards

Application	LED
Operating Temperature standard	-20C (-4F) to a maximum of +40C (+104F) cULus - Certified;cULus - Listed