



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S1214V 12-10AWG 1/4\"STD InsIt'd Fork TRML

Nsi Industries

Catalog Number	S1214V
Manufacturer	Nsi Industries
Description	Tin-Plated Copper Spade Terminal Is Insulated With Vinyl and Has An Open Tongue End For Rapid Insertion On The Mounting Screw. Used For Wire Termination In Applications With 1/4" Stud and 12-10 Awg.
Weight per unit	0.2620 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper/PVC
Number of Terminals	1
Terminal Size	1/4
Voltage Rating	300
Warranty	1 YEAR
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

Descriptions

Description	12-10AWG 1/4\"STD INSLTD FORK TRML
extra long description	NSI S12-14V 12-10 Vinyl LockSpade 5
Features	12-10 AWG Vinyl Insulated Spade 1/4" Stud, 50 Per Pack
Long Description	Tin-plated Copper Spade terminal is insulated with vinyl and has an open tongue end for rapid insertion on the mounting screw. Used for wire termination in applications with 1/4" Stud and 12-10 AWG.
Product Type	12-10 Vinyl Lockspade 50 Pack # 6 Stud
Special Features	Vinyl Insulated Spade Terminal 12-10 AWG - 50 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381062123
Manufacturers Part Number	S12-14V
UPC	662381062123

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Vinyl Insulated Spade Terminal



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 50

Packaging

Carton 1

Package 50

Weight Per package 0.262

Uses, Certifications, and Standards

Application Wire Termination

environmental conditions 75 C

standard cULus