



# S1904

F8T5/CW  
8 watt; T5; Preheat Fluorescent; 4000K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1904

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S1904	045923019043	8	T5	Miniature Bi Pin	G5	F8T5/CW	0.63"

MOL In Inches	Nominal Length	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	CRI
11.91"	12"	380	5000	4000	Cool White	500/10	62

RoHS Compliant
Yes



<p>National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com</p>	<p>Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico</p>	<p>Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027</p>	
--	--	---	--



# S1904

F8T5/CW  
8 watt; T5; Preheat Fluorescent; 4000K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1904

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S1904	045923019043	8	T5	Miniature Bi Pin	G5	F8T5/CW	0.63"

MOL In Inches	Nominal Length	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	CRI
11.91"	12"	380	5000	4000	Cool White	500/10	62

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

