



S1928

LU1000/ET25
1000 watt; High Pressure Sodium HID; Mogul base; ET25;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1928

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|--------------|-------|------------|-------|-----------|-----------|-------------|
| S1928 | 045923019289 | 1000 | ET25 | Mogul | E39 | S52 | LU1000/ET25 |

| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
|--------|---------------|---------------|---------------------|----------------|-------------|------|-----|
| Clear | 15.06" | 3.13" | 24000 | 130000 | 2100 | 12 | 22 |

| Burning Position | RoHS Compliant |
|------------------|----------------|
| Universal | Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S1928

LU1000/ET25
1000 watt; High Pressure Sodium HID; Mogul base; ET25;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1928

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|--------------|-------|------------|-------|-----------|-----------|-------------|
| S1928 | 045923019289 | 1000 | ET25 | Mogul | E39 | S52 | LU1000/ET25 |

| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
|--------|---------------|---------------|---------------------|----------------|-------------|------|-----|
| Clear | 15.06" | 3.13" | 24000 | 130000 | 2100 | 12 | 22 |

| Burning Position | RoHS Compliant |
|------------------|----------------|
| Universal | Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

