



S1931

LU100
100 watt; High Pressure Sodium HID; Mogul base; ET23 1/2;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1931

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|------------------|---------------|---------------|---------------------|----------------|-------------|-----------|-----------|
| S1931 | 045923019319 | 100 | ET23.5 | Mogul | E39 | S54 | LU100 |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
| Clear | 7 3/4" | 2.94" | 24000 | 24000 | 2100 | 12 | 22 |
| Burning Position | | | | RoHS Compliant | | | |
| Universal | | | | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S1931

LU100
100 watt; High Pressure Sodium HID; Mogul base; ET23 1/2;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1931

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|------------------|---------------|---------------|---------------------|----------------|-------------|-----------|-----------|
| S1931 | 045923019319 | 100 | ET23.5 | Mogul | E39 | S54 | LU100 |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
| Clear | 7 3/4" | 2.94" | 24000 | 24000 | 2100 | 12 | 22 |
| Burning Position | | | | RoHS Compliant | | | |
| Universal | | | | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

