



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S20N11P01P 1KVA Type Ep Transformer 1PH 240X480-120/240V

Eaton Corp

Catalog Number	S20N11P01P
Manufacturer	Eaton Corp
Description	Dry Type Transformer, 240 X 480 V, 120/240 V, 1 K Va Va Rating, Encapsulated Transformer, 6.32 In Overall Length, 13.03 In Overall Height, 60 HZ, 115 °C Temperature Rise Rating, 28.61 LB
Weight per unit	28.6 (lbs/each)
Product Category	Single Phase Non Ventilated to

### Features

design	EP
dimensions	6.5600 IN X 5.5300 IN X 13.0300 IN
kva rating	1 kVA
Number of Phases	Single-phase
Tap Size	NONE

### Descriptions

Description	1KVA TYPE EP TRANSFORMER 1PH 240X480-120/240V
extra long description	ETN S20N11P01P 1KVA TYPE EP XFMR 1P
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.

### Manufacturer Information

GTIN	00786680073687
UPC	786680073687

### Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Encapsulated transformer

### Packaging

Carton	1
Weight Per each	28.61



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Frequency Rating	60 Hz
Mounting standard	WALL UL Listed
Temperature Rating	115 °C rise