

Specifications

Photo is representative



Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

Physical Attributes

COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20N11P01P
UPC	786680073687
PRODUCT LENGTH/DEPTH	6.56 in
PRODUCT HEIGHT	13.03 in
PRODUCT WIDTH	5.53 in
PRODUCT WEIGHT	25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

