

# Eaton S20N11P76P

Catalog Number: S20N11P76P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 kVA, Alum windings, Frame: 58AP, Indoor-Outdoor

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11P76P
	UPC
	786680233852
<b>Product Length/Depth</b>	<b>Product Height</b>
5.99 in	11.68 in
<b>Product Width</b>	<b>Product Weight</b>
4.99 in	22 lb
<b>Compliances</b>	<b>Certifications</b>
Not Applicable	UL Listed

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

58AP

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.75 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - S20N11P76P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton S20N11P76P

Catalog Number: S20N11P76P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 kVA, Alum windings, Frame: 58AP, Indoor-Outdoor

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11P76P
	UPC
	786680233852
<b>Product Length/Depth</b>	<b>Product Height</b>
5.99 in	11.68 in
<b>Product Width</b>	<b>Product Weight</b>
4.99 in	22 lb
<b>Compliances</b>	<b>Certifications</b>
Not Applicable	UL Listed

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

58AP

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.75 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - S20N11P76P](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)