

Eaton S20N11P76P

Catalog Number: S20N11P76P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 kVA, Alum windings, Frame: 58AP, Indoor-Outdoor

General specifications



Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20N11P76P
	UPC
	786680233852
Product Length/Depth	Product Height
5.99 in	11.68 in
Product Width	Product Weight
4.99 in	22 lb
Compliances	Certifications
Not Applicable	UL Listed

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

58AP

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

0.75 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Specifications and datasheets

[Eaton Specification Sheet - S20N11P76P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)