



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S21362 5 Watt ST19 Led Lamp - CL

Satco

Catalog Number	S21362
Manufacturer	Satco
Description	5 Watt ST19 Led Lamp - Clear - Medium Base - 90 Cri - 4000K - 120 Volts
Weight per unit	0.1500 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26
beam angle	300
dimnable	Yes-Dimmable
lumens	425
Power Factor	0.75
Voltage Rating	120
Wattage	5

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	4000

Descriptions

Description	5 WATT ST19 LED LAMP - CL
extra long description	SATCO S21362 5ST19/CL/LED/940/E26
Long Description	5 Watt ST19 LED Lamp - Clear - Medium Base - 90 CRI - 4000K - 120 Volts
Product Type	5ST19/CL/Led/940/E26
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: 120V only ; Material: Glass / Nickel Plated Aluminum ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Cool White ; Efficacy: 85.00 LPW ; DLC Approved: False ; FCC Compliant: True ; NSF Approved: No ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.055A

Manufacturer Information

Brand	Satco
GTIN	00045923206696
Manufacturers Part Number	S21362
UPC	045923206696



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight Per each	0.15

Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Listed