

# S29390 n/a LED

18W/LED/HID/5000K/100-277V  
E26

|                   |      |
|-------------------|------|
| Lamp Type         | LED  |
| Base Type         | E26  |
| Wattage           | 18   |
| Color Temperature | 5000 |



IMAGE NOT AVAILABLE

## Product Specifications

| Item Number | Technology                     | UPC                   | Voltage         | Watts         | Incandescent Equivalent | Lamp Shape     | Base                |
|-------------|--------------------------------|-----------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| S29390      | LED                            | *20045923293904       | 100-277         | 18            | 120                     | n/a            | Medium              |
| ANSI Base   | Lamp Code                      | Dimmable/Non-Dimmable | Finish          | MOL in inches | MOD in inches           | Initial Lumens | Average Rated Hours |
| E26         | 18W/LED/HID/5000K/100-277V/E26 | n/a                   | n/a             | 6 25/32       | 2 3/4                   | n/a            | 50000               |
| Kelvin Temp | Color                          | CRI                   | Beam Spread Deg | Pack          | Package Type            | ENERGY STAR    | RoHS Compliant      |
| 5000        | Natural Light                  | n/a                   | 300             | 24            | n/a                     | n/a            | Yes                 |