

# S29391 n/a LED

22W/LED/HID/5000K/100-277V  
E26

Lamp Type	LED
Base Type	E26
Wattage	22
Color Temperature	5000



IMAGE NOT AVAILABLE

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29391	LED	*20045923293911	100-277	22	150	n/a	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	22W/LED/HID/5000K/100-277V/E26	n/a	n/a	7 9/16	2 3/4	n/a	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	n/a	300	24	n/a	n/a	Yes