

Project Name

Location

Prepared By



## SATCO S29391

22W/LED/HID/5000K/100-277V E26

### Notes

(www) 18-27-2023 05:20:50

### General

|                         |                                            |
|-------------------------|--------------------------------------------|
| Status                  | Obsolete                                   |
| Substitute              | S49391                                     |
| Watts                   | 22W                                        |
| Incandescent Equivalent | 150W                                       |
| Fluorescent Equivalent  | 40W                                        |
| HID Equivalent          | 100W                                       |
| Volts                   | 120V-277V                                  |
| Shape                   | Corncob                                    |
| Base                    | Medium                                     |
| ANSI Base               | E26                                        |
| Finish                  | Clear                                      |
| CCT (Kelvin)            | 5000K                                      |
| Temperature             | Natural Light                              |
| CRI                     | 80+                                        |
| Lumens                  | 2950L                                      |
| Beam Spread             | 300                                        |
| Dimmable                | Non-Dimmable                               |
| Hours Rated             | 50000                                      |
| Product Category        | Corncob                                    |
| Technology              | LED                                        |
| Min Compartment Size    | Length: 8.5 in. Width: 6 in. Depth: 6 in.  |
| Ballasting Requirements | Ballast Bypass- Direct wire only 100V-277V |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Working Voltage       | AC 90-305V                 |
| Operating Frequency   | 50/60Hz                    |
| Power Factor          | >.9                        |
| Operating Position    | Universal                  |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

### Physical

|              |       |
|--------------|-------|
| MOL          | 7.56  |
| MOD          | 2.75  |
| Lens Finish  | Clear |
| Weight (lb.) | 0.96  |

### Additional Information

|                            |                                                                                                                                                        |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Info            | Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg) |
| Rated For Enclosed Fixture | Yes                                                                                                                                                    |
| IP Rating                  | IP65                                                                                                                                                   |
| Installation Notes         | Not for use in vapor tight fixtures.                                                                                                                   |
| Warranty                   | 5-Years                                                                                                                                                |

### Compliance

|                      |                                                       |
|----------------------|-------------------------------------------------------|
| Safety Listing       | cULus - Certified; cULus - Classified; cULus - Listed |
| Location Rating      | Damp                                                  |
| DLC Approved         | No                                                    |
| California Status    | Lawful for sale in California                         |
| Title 20 / 24 Status | Lawful for sale                                       |
| Colorado Status      | Lawful for sale                                       |
| Hawaii Status        | Lawful for sale                                       |
| Nevada Status        | Lawful for sale                                       |
| Vermont Status       | Lawful for sale                                       |
| Washington Status    | Lawful for sale                                       |
| RoHS Compliant       | Yes                                                   |
| FCC Compliant        | Yes                                                   |
| SDS Sheet            | LED_Lamp                                              |