

Project Name

Location

Prepared By



SATCO S29406

6.5PAR20/LED/40°/930/120V

Notes

(www) 18-27-2023 05:20:07

General

Status	Active
Watts	6.5W
Incandescent Equivalent	50W
Fluorescent Equivalent	11W
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90+
Lumens	520L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	593
Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	2.99
MOD	2.44
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic (PBT)
Housing Color	Silver
Weight (lb.)	0.13

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5-Years

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp