

Project Name

Location

Prepared By



SATCO S29454

15PAR38/LED/60°/950/120V

Notes

(www) 18-27-2023 05:20:07

General

Status	Active
Watts	15W
Incandescent Equivalent	90W
Fluorescent Equivalent	23W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90+
Lumens	1200L
Beam Spread	60
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	876
Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5
MOD	4.72
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic (PBT)
Housing Color	Silver
Weight (lb.)	0.49

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5-Years

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp