



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29558 9.5W Led A19 40K Non-Dim 800LM 4-Pack

Satco

| | |
|------------------|---|
| Catalog Number | S29558 |
| Manufacturer | Satco |
| Description | 9.5W A19 Led Lamp Frosted 40K E26 220' Beam 120V Non-Dimmable 4-PK |
| Weight per unit | 0.5500 (lbs/each) |
| Product Category | Led A-Line A Shape Lamps |

Features

| | |
|----------------|--------------------------------|
| average life | 15000 |
| Base | Medium |
| beam angle | 220 |
| dimmable | No |
| lumens | 800 |
| Shape | A19 |
| Voltage Rating | 120 |
| Warranty | 3 Year Limited - 10 hr per day |
| Wattage | 10 |

Material, Color, and Finish

| | |
|-------------------|------|
| color temperature | 4000 |
|-------------------|------|

Dimensions and Weight

| | |
|----------|------|
| Diameter | 2.38 |
| Length | 4.38 |

Descriptions

| | |
|------------------------|---|
| Description | 9.5W LED A19 40K NON-DIM 800LM 4-PACK |
| extra long description | SATCO S29558 9.5A19/LED/40K/ND/120V |
| Long Description | 9.5W A19 LED Lamp Frosted 40K E26 220' Beam 120V Non-Dimmable 4-PK |
| Product Type | 9.5A19/Led/40K/ND/120V/4PK |
| Special Features | Enclosed fixture rated: Yes ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Energy Star rated: Yes ; Lamp appearance: Frosted White ; Incandescent equivalent: 60 watts |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923295584 |
| Manufacturers Part Number | S29558 |
| UPC | 045923295584 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Type Type A

Packaging

Carton 1

Package 12

Weight Per each 0.55

Uses, Certifications, and Standards

Operating Temperature -25C (-13F) to a maximum of +45C (+113F)