

S29816 A19 LED

15A19/LED/3000K/1600L/120V/D

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	15
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	1600 lumens
Estimated Energy Cost	\$1.81
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	15 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29816	LED	*20045923298169	120	15	100	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	15A19/LED/3000K/1600L/120V/D	Yes	n/a	4 5/8	2 3/8	1600	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes

S29816 A19 LED

15A19/LED/3000K/1600L/120V/D

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	15
Color Temperature	3000
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	1600 lumens
Estimated Energy Cost	\$1.81
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	15 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29816	LED	*20045923298169	120	15	100	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	15A19/LED/3000K/1600L/120V/D	Yes	n/a	4 5/8	2 3/8	1600	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes